

Screw Fittings

Brass

Sockets



RoHS10

Type	Material
SJSFS	C3604

Female/Male Sockets



RoHS10

Type	Material
SJSXS	C3604

Nipples



RoHS10

Type	Material
SJSRN	C3604

Caps



RoHS10

Type	Material
SJSCP	C3604

Female/Male Elbows



RoHS10

Type	Material
SJSXL	C3771

Elbows



RoHS10

Type	Material
SJSFL	C3771

Male Elbows



RoHS10

Type	Material
SJSML	C3771

Tees



RoHS10

Type	Material
SJSFT	C3771

Part Number	Rc (PT)	L	L1	B	Unit Price	Volume Discount Rate
Type	No.				1 ~ 9 pc(s).	10~20 pcs.
SJSFS	6A	1/8	21	10.5	14	
	8A	1/4	28	14	17	
	10A	3/8	32	16	21	
	15A	1/2	40	20	26	

For orders larger than indicated quantity, please check with WOS.

Part Number	Rc (PT)	R (PT)	L	d	B	Unit Price	Volume Discount Rate
Type	No.	T1	T2			1 ~ 9 pc(s).	10~20 pcs.
SJSXS	6A	1/8	1/8	20	5	14	
	8A	1/4	1/4	24	8	17	
	10A	3/8	3/8	28	11	21	
	15A	1/2	1/2	33	15	26	

For orders larger than indicated quantity, please check with WOS.

Part Number	R (PT)	L	B	Unit Price	Volume Discount Rate
Type	No.			1 ~ 9 pc(s).	10~20 pcs.
SJSRN	6A	1/8	22	12	
	8A	1/4	28	14	
	10A	3/8	33	17	
	15A	1/2	38	22	

For orders larger than indicated quantity, please check with WOS.

Part Number	Rc (PT)	L	L1	B	Unit Price	Volume Discount Rate
Type	No.				1 ~ 9 pc(s).	10~20 pcs.
SJSCP	6A	1/8	9	7	12	
	8A	1/4	11	9	16	
	10A	3/8	14	12	19	
	15A	1/2	15	13	24	

For orders larger than indicated quantity, please check with WOS.

Part Number	R, Rc (PT)	L1	L2	Unit Price	Volume Discount Rate
Type	No.			1 ~ 9 pc(s).	10~20 pcs.
SJSXL	6A	1/8	19	22	
	8A	1/4	24	25	
	10A	3/8	28	29	
	15A	1/2	32	34	

For orders larger than indicated quantity, please check with WOS.

Part Number	Rc (PT)	L1	L2	Unit Price	Volume Discount Rate
Type	No.			1 ~ 9 pc(s).	10~20 pcs.
SJSFL	6A	1/8	22	22	
	8A	1/4	25	25	
	10A	3/8	29	29	
	15A	1/2	34	34	

For orders larger than indicated quantity, please check with WOS.

Part Number	R (PT)	L1	L2	Unit Price	Volume Discount Rate
Type	No.			1 ~ 9 pc(s).	10~20 pcs.
SJSML	6A	1/8	17	17	
	8A	1/4	22	22	
	10A	3/8	25	25	
	15A	1/2	29	29	

For orders larger than indicated quantity, please check with WOS.

Part Number	Rc (PT)	L	L1	Unit Price	Volume Discount Rate
Type	No.			1 ~ 9 pc(s).	10~20 pcs.
SJSFT	6A	1/8	44	22	
	8A	1/4	50	25	
	10A	3/8	58	29	
	15A	1/2	68	34	

For orders larger than indicated quantity, please check with WOS.

Male Tees



RoHS10

Type	Material
SJSMT	C3771

Female/Male Tees



RoHS10

Type	Material
SJSXT	C3771


Plugs



RoHS10

Type	Material
SJSPG	C3604

Reducing Hex Sockets



RoHS10

Type	Material
SJSFSD	C3604

Reducing Female/Male Sockets



RoHS10

Type	Material
SJSXSD	C3604

Reducing Hex Nipples



RoHS10

Type	Material
SJSRND	C3604

Bushings



RoHS10

Type	Material
SJSPB	C3604

Part Number	R (PT)	L	L1	Unit Price	Volume Discount Rate
Type	No.			1 ~ 9 pc(s).	10~20 pcs.
SJSMT	6A	1/8	34	17	
	8A	1/4	44	22	
	10A	3/8	50	25	
	15A	1/2	58	29	

For orders larger than indicated quantity, please check with WOS.

Part Number	R Rc (PT)	L	L1	L2	Unit Price	Volume Discount Rate
Type	No.				1 ~ 9 pc(s).	10~20 pcs.
SJSXT	6A	1/8	44	22	19	
	8A	1/4	50	25	24	
	10A	3/8	58	29	28	
	15A	1/2	68	34	32	

For orders larger than indicated quantity, please check with WOS.

Part Number	R (PT)	L	B	Unit Price	Volume Discount Rate
Type	No.			1 ~ 9 pc(s).	10~20 pcs.
SJSPG	6A	1/8	14	12	
	8A	1/4	18	16	
	10A	3/8	21	19	
	15A	1/2	25	21	

For orders larger than indicated quantity, please check with WOS.

Part Number	Rc (PT)	L	B	Unit Price	Volume Discount Rate
Type	No.	T1	T2	1 ~ 9 pc(s).	10~20 pcs.
SJSFSD	12	1/8	1/4	26	17
	13	1/8	3/8	28	21
	23	1/4	3/8	30	21
	24	1/4	1/2	36	26
	34	3/8	1/2	38	26
	36	3/8	3/4	44	32
	46	1/2	3/4	46	32

For orders larger than indicated quantity, please check with WOS.

Part Number	R (PT)	Rc (PT)	L	B	Unit Price	Volume Discount Rate
Type	No.	T1	T2		1 ~ 9 pc(s).	10~20 pcs.
SJSXSD	12	1/8	1/4	22	17	
	21	1/4	1/8	22	14	
	23	1/4	3/8	26	21	
	32	3/8	1/4	26	17	
	34	3/8	1/2	31	26	
	43	1/2	3/8	30	22	

For orders larger than indicated quantity, please check with WOS.

Part Number		R (PT)		L	B	Unit Price 1 - 9 pc(s).	Volume Discount Rate 10-20 pcs.
Type	No.	T1	T2				
SJSRND	12	1/8	1/4	26	14		
	13	1/8	3/8	29	17		
	23	1/4	3/8	31	17		
	24	1/4	1/2	34	22		
	34	3/8	1/2	36	22		
	36	3/8	3/4	41	27		
	46	1/2	3/4	43	27		

For orders larger than indicated quantity, please check with WOS.

Part Number	Rc (PT)	R (PT)	L	B	Unit Price	Volume Discount Rate
Type	No.	T1	T2		1 ~ 9 pc(s).	10~20 pcs.
SJSPB	12	1/8	1/4	16	17	
	13	1/8	3/8	19	19	
	23	1/4	3/8	19	19	
	24	1/4	1/2	21	24	
	34	3/8	1/2	21	24	
	36	3/8	3/4	25	30	
	46	1/2	3/4	25	30	

For orders larger than indicated quantity, please check with WOS.



Fitting Specifications

Operating Temperature Range
Max. Operating Pressure

-50 ~ 150°C (No Freezing)
6.9MPa



Ordering Example

Part Number
SJSMT6A