


## Economy Type Post-Assembly Insertion Screws / Pre-Assembly Insertion Screws for Aluminum Extrusions

For 8 Series (Slot Width 10mm)



Economy Type of Post-Assembly Insertion Screw is offered. (This type is priced approx. 40% lower than HATLSN8-8 of Post-Assembly Insertion Screw.) **Tightening Torque** **P552**

**Economy Type Post-Assembly Insertion Screw**


**Material** SWRCH35K  
(Carbon Steel Wire Rod)  
**Surface Treatment:** Trivalent Chromate  
**RoHS10**

**HATL8-8**

**Effective Length of Economy Type Post-Assembly Insertion Screws**

Part Number	L	H	Applicable Extrusion (Series)	Reference Tightening Torque (N·m)	Unit Price	Volume Discount Rate	
					1-29 pc(s)	30-149	150-600
<b>HATL8-8</b>	20	17.0	8 Series 8-45 Series	23.5			
	25	22.0					

Ordering Example: Part Number - L  
Example: **HATL8-8** - 20



**Post-Assembly Insertion Screw**

**Material** Nut Screw  
SUS316 Equivalent (Sintered)  
SUS304  
**RoHS10**

**HATLSN8-8**

**Effective Length of Post-Assembly Insertion Screws**

Part Number	L	H	Applicable Extrusion (Series)	Reference Tightening Torque (N·m)	Unit Price	Volume Discount Rate	
					1-29 pc(s)	30-149	150-600
<b>HATLSN8-8</b>	20	17.0	8 Series 8-45 Series	23.5			
	25	22.0					

Ordering Example: Part Number - L  
Example: **HATLSN8-8** - 20

**Pre-Assembly Insertion Screw**

**Material** Nut Screw  
SUS316 Equivalent (Sintered)  
SUS304  
**RoHS10**

**HNTLSN8-8**

**Effective Length of Pre-Assembly Insertion Screws**

Part Number	L	H	Applicable Extrusion (Series)	Reference Tightening Torque (N·m)	Unit Price	Volume Discount Rate	
					1-29 pc(s)	30-149	150-600
<b>HNTLSN8-8</b>	20	17.5	8 Series 8-45 Series	23.5			
	25	22.5					

Ordering Example: Part Number - L  
Example: **HNTLSN8-8** - 20

**Flanged Nuts**

**Material:** SUS304  
**RoHS10**

**HTDN**

**Effective Length of Pre-Assembly Insertion Screws**

Part Number	Type	M	B	T	D	Unit Price	Volume Discount Rate	
						1-499 pc(s)	500-999	1000-1500
<b>HTDN</b> (Stainless Steel)	4	7	4.2	10				
	5	8	5.5	12				
	6	10	6.0	13				
	8	12	7.5	17				

Ordering Example: Part Number  
Example: **HTDN6**