



Pipe Supports

-Hanger Bands Standard Type / With Eye Bolt Type / Eye Bolt-


CAD Data Folder Name: 51_Hollows_Fittings_Valves

Hanging Band


RoHS

Type	Material	Surface Treatment
Standard	With eye bolt hole	
TBND	TBND	SPHC
TBND	TBND	Trivalent Chromate
TBND	TBND	SUS304

Standard



With eye bolt hole



Part Number	Type	No.	Hollow Outer Dia. D	(L)	t	W	D1	F	TBND		TBND	
									Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
Standard TBND TBND	15A	21.7	62	1.8 (2)	25	26	6 (8)		64	37	132	101
	20A	27.2	65						69	41	137	105
	25A	34	72						73	46	142	110
	32A	42.7	81						78	51	160	128
	40A	48.6	87						82	55	178	146

Dimensions in () are applicable to SUS304.

Part Number	Type	No.	Hollow Outer Dia. D	(L)	t	W	D1	H	Diameter of Eye Bolt	TBND		TBND	
										Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
With eye bolt hole TBND TBND	15A	21.7	95	1.8 (2)	25	26	71(72)	65	W3/8	146	73	210	201
	20A	27.2	98					68		152	76	214	205
	25A	34	105					76		158	79	219	210
	32A	42.7	114					76		217	109	228	219
	40A	48.6	120					79		240	120	233	223



Dimensions in () are applicable to SUS304.

Diameter of eye bolt W3/8 indicates BSW. For fixing, use eye bolts.

Eye Bolt


RoHS

Type	Material	Surface Treatment
TBNN	SPHC	Trivalent Chromate
TBNN	SUS304	-



Part Number	Type	L	Applicable Diameter of Eye Bolt W	TBNN		TBNN	
				Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
TBNN TBNN	1000	W3/8		160	137	205	182

Diameter of eye bolt 3/8. indicates BSW.



Low Pressure Screw Fittings

-With Seal Coating Type-

CAD Data Folder Name: 51_Hollows_Fittings_Valves


Features: Seal coating on thread part. Provides immediate out of the box operation.

Steel Hollow Fittings

RoHS



Type	Material	Surface Treatment
SGCEL	FCMB270	Hot Zinc Plating
SUCEL	SUS304	-




Allowable temperature for With Seal Coating Type is 150°C

Steel Hollow Fittings

RoHS



Type	Material	Surface Treatment
SGCPP	FCMB270	Hot Zinc Plating
SUCPP	SUS304	-




Allowable temperature for With Seal Coating Type is 150°C

Steel Hollow Fittings

RoHS



Type	Material	Surface Treatment
SGCNP	SGP	Hot Zinc Plating
SUCNP	SUS304	-




Allowable temperature for With Seal Coating Type is 150°C

Steel Hollow Fitting

RoHS



Type	Material	Surface Treatment
SGCNR	FCMB270	Hot Zinc Plating
SUCNR	SUS304	-




Allowable temperature for With Seal Coating Type is 150°C

Steel Hollow Fittings

RoHS



Type	Material	Surface Treatment
SGCPB	FCMB270	Hot Zinc Plating
SUCPB	SUS304	-



Allowable temperature for With Seal Coating Type is 150°C

Part Number	Type	No.	R Rc (PT)	SGCEL		SUCEL		SGCEL		SUCEL	
				(D)	(L1)	(L2)	(L2)	A	B	Unit Price	Volume Discount Rate
SGCEL SUCEL	6A	1/8	19	23	36	17	26	14.5	22	33	17
	8A	1/4	22	26	42	19	30	21	26	41	19
	10A	3/8	27	31	48	23	35	25	32	48	23
	15A	1/2	31	38	56	27	40	29	38	55	27
	20A	3/4	36	45	66	32	47	36	46	65	32

Part Number		R(PT)	Opposite Side H	t	L		SGCPP		SUCPP	
Type	No.				SGCPP	SUCPP	Unit Price 1~9	Volume Discount Rate 10~	Unit Price 1~19	Volume Discount Rate 20~
SGCPP SUCPP	6A	1/8	7	7	16	16	137	123	142	128
	8A	1/4	9	8	19	19	114	105	119	105
	10A	3/8	12	9	21	21	123	110	128	114
	15A	1/2	14	10	26	25	137	123	142	128
	20A	3/4	17	11	29	28	146	132	210	192
	25A	1	19	12	31	31	223	205	219	201

Part Number		R (PT)	D	L	d		SGCNP		SUCNP	
Type	No.				SGCNP	SUCNP	Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
					1~9	10~	1~19	20~		
SGCNP SUCNP	6A	1/8	10.5	24	6.5	6.5	151	137	155	142
	8A	1/4	13.8	26	8.7	9.7	151	137	155	142
	10A	3/8	17.3	28	12.1	13.1	160	146	164	151
	15A	1/2	21.7	34	15.8	15.5	160	146	164	151
	20A	3/4	27.2	38	21.6	21.3	169	155	173	155
	25A	1	34	42	27.8	28.1	192	173	196	178

Part Number		R (PT)	B	L	(ℓ)	d		SGCNR		SUCNR	
Type	No.					SGCNR	SUCNR	Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
SGCNR SUCNR	8A	1/4	17	34	12	7	7	1~9	10~	1~19	20~
	10A	3/8	21	36	13	9	9	114	105	155	142
	15A	1/2	26	42	16	13	13	123	110	182	164
	20A	3/4	32	47	18	18	16	137	123	269	246
	25A	1	38	52	20	24	22	178	160	301	273

Part Number		Rc (PT)	R (PT)	SGCPB		SUCPB		SGCPB		SUCPB	
Type	No.	T ₁	T ₂	L	B	L	B	Unit Price 1~9	Volume Discount Rate 10~	Unit Price 1~19	Volume Discount Rate 20~
SGCPB SUCPB	12	1/8	1/8	17	17	17	20	119	105	123	110
	13	1/8	3/8	18	21	18	24	119	105	123	110
	23	1/4	3/8	18	21	18	24	119	105	123	110
	24	1/4	1/2	21	26	21	30	146	132	151	137
	34	3/8	1/2	21	26	21	30	151	137	155	142
	36	3/8	3/4	24	32	24	37	164	151	182	164
	46	1/2	3/4	24	32	24	37	182	164	205	187

Cautions
1. Not applicable for steam plumbing.
2. Used Fittings cannot be reused (due to impaired function of the seal coating resin)

