


Rack Gears - L Fixed

Pressure Angle 20°, Module 0.5, 0.8, 1.0, 1.5, 2.0, 2.5, 3.0

Rack Gears - L Configurable (One End Machined)

Pressure Angle 20°, Module 0.5, 0.8, 1.0, 1.5, 2.0, 2.5, 3.0



Part Number		Nominal	Hole Machining	Number of Effective Teeth	L	P (Pitch)	W	H	h	B (Hole Pitch)	M (Coarse)	d1	d2	Z1	K (Number of Holes)	Unit Price				
Type	Module															Both Ends Machined Type				