

Toggle Clamps

Hold Down, Horizontal Standard Handle (Straight Base)

1N=0.101972kgf

Hold Down, Horizontal Standard Handle (Straight Base)




(Clamped)

Part Number	MC01-1S
Body Material	SS400
Surface Treatment	Trivalent Chromate
Tightening Force (N)	264.6
Weight (g)	30
Arm Open-Close Angle	90°
Handle Open-Close Angle	75°
Accessory	* Nylon Bolt
Unit Price	

MC01-1S

* Not a bolt with rubber.



Hold Down, Horizontal Standard Handle (Straight Base)




(Clamped)

Part Number	MC01-2S
Body Material	SS400
Surface Treatment	Trivalent Chromate
Tightening Force (N)	264.6
Weight (g)	35
Arm Open-Close Angle	90°
Handle Open-Close Angle	75°
Accessory	* Nylon Bolt
Unit Price	

MC01-2S

* Not a bolt with rubber.




Hold Down, Horizontal Standard Handle (Straight Base)



(Clamped)

Part Number	MC01-3S
Body Material	SS400
Surface Treatment	Trivalent Chromate
Tightening Force (N)	882
Weight (g)	130
Arm Open-Close Angle	85°
Handle Open-Close Angle	73°
Accessory	Bolt with Rubber Material: NBR Hardness: Shore A70
Unit Price	

MC01-3S




Hold Down, Horizontal Standard Handle (Straight Base)



(Clamped)

Part Number	MC01-4S
Body Material	SS400
Surface Treatment	Trivalent Chromate
Tightening Force (N)	2352
Weight (g)	265
Arm Open-Close Angle	90°
Handle Open-Close Angle	65°
Accessory	Bolt with Rubber Material: NBR Hardness: Shore A70
Unit Price	

MC01-4S



Ordering Example

Part Number
MC01-1S

Toggle Clamps

Hold Down, Horizontal Long Handle (Flange Base)

1N=0.101972kgf

Hold Down, Horizontal Long Handle (Flange Base)




(Clamped)

Part Number	MC01L-1
Body Material	SS400
Surface Treatment	Trivalent Chromate
Tightening Force (N)	264.6
Weight (g)	35
Arm Open-Close Angle	90°
Handle Open-Close Angle	75°
Accessory	* Nylon Bolt
Unit Price	

MC01L-1

* Not a bolt with rubber.




Hold Down, Horizontal Long Handle (Flange Base)



(Clamped)

Part Number	MC01L-3
Body Material	SS400
Surface Treatment	Trivalent Chromate
Tightening Force (N)	882
Weight (g)	140
Arm Open-Close Angle	85°
Handle Open-Close Angle	73°
Accessory	Bolt with Rubber Material: NBR Hardness: Shore A70
Unit Price	

MC01L-3



Hold Down, Horizontal Long Handle (Flange Base)




(Clamped)

Part Number	MC01L-2
Body Material	SS400
Surface Treatment	Trivalent Chromate
Tightening Force (N)	264.6
Weight (g)	40
Arm Open-Close Angle	90°
Handle Open-Close Angle	75°
Accessory	* Nylon Bolt
Unit Price	


MC01L-2

* Not a bolt with rubber.



Example


Clamp for LCD Continuity Tests of Mobile Phones.



Long Handle Features (Comparison with Conventional Products)

Conventional Products

Long Handle



Pinch hazard!

Long arm is safer to use, thus resulting in increased operability.



Ordering Example

Part Number
MC01L-1