


Knurled Plastic Knob Screws / Knurled Plastic Handwheels

Knurled




Part Number		L Selection		Knob Color	Lf		H	H1	S	S1	d	d1	Reference Mass (g)			Unit Price					
Type	M (Coarse) - D	NBM, NBLM NBMS, NBLMS			NBF	NBLF							NBM	NBF	NBLM	NBLF	NBMS	NBLMS			
NBM NBMS NBF Stepped Type NBLM NBLMS NBLF	3-16	10 15		B (Black) W* (White)	5	10	12	16	2	6	11	9	10	5	10						
	4-16	10 15			6	15	14	20.5	4	9.5	15	10	15	6	15						
	5-16	10 15 20			9	16	18	27	6	15	19	10	19	9	19						
	5-20	15 20			6	15	14	20.5	4	9.5	15	19	15	6	15						
	5-25	20 25			9	16	18	27	6	15	19	10	19	9	19						
	6-20	10 15 20			6	15	14	20.5	4	9.5	15	19	15	6	15						
	6-25	15 20 25			9	16	18	27	6	15	19	10	19	9	19						
	6-32	20 25			9	16	18	27	6	15	19	10	19	9	19						
NBMR	8-32	15 25			9	16	18	27	6	15	19	10	19	9	19						
	8-32	15 25			9	16	18	27	6	15	19	10	19	9	19						

* White is available for NBM, NBF, NBLM and NBLF only. The default color will be black unless specified.

Knobs Made by Nylon (NBMR)

Part Number		L Selection		Knob Color	H	S	d	d1	Reference Mass (g)	Unit Price
Type	M (Coarse) - D	NBM, NBLM NBMS, NBLMS								
NBMR	5-20	10		B (Black)	14	4	15	10	15	
	6-20	25			14	4	15	10	15	
	8-25	16 25			18	6	24	12	29	
	8-32	20			18	6	24	12	29	

Ordering Example	Part Number	-	L	-	Knob Color
	NBM3-16	-	15	-	B
	NBM5-20	-	20	-	W
	NBMR8-32	-	20	-	B




Part Number		L Selection		Knob Color	H	S	d	R	Lr	h	P	B	G	M	Mass (g)		Unit Price	
Type	D	NBM, NBLM NBMS, NBLMS													CHBK	CHBKN	CHBK	CHBKN
CHBK CHBKN	40	20	13	7	18.5	6	15	4	13	13	18.8	4	30	22	45	37		
	50	25	17	8	20	8	19	5	17.5	13	20.8	5	30	22	65	58		
	63	29	20	9	23	8	22	6	22	14	23.8	6	30	22	97	84		
	80	36	24	12	28	12	27	6	30	16	23.8	6	30	22	97	84		


Ordering Example	Part Number	-	L	-	Knob Color
	CHBK40	-	10	-	B

Knurled Plastic Knob Screws / Knurled Plastic Knob Screws - Large Diameter

Diamond Cut



Part Number		L Selection		Knob Color	Lf		H	H1	S	S1	d	d1	Reference Mass (g)			Unit Price					
Type	M (Coarse) - D	NBMX, NBLMX NBMSX, NBLMSX			NBFX	NBLFX							NBMX	NBFX	NBLMX	NBLFX	NBMSX	NBLMSX			
Standard NBMX NBMSX NBFX Stepped Type NBLMX NBLMSX NBLFX	3-16	10 15		B (Black) W* (White)	5	10	12	16	2	6	11	9	10	5	10						
	4-16	10 15			6	15	14	22	4	12	15	10	15	6	15						
	5-16	10 15 20			9	16	18	27	6	15	19	10	19	9	19						
	5-20	15 20			6	15	14	22	4	12	15	19	15	6	15						
	5-25	20 25			9	16	18	27	6	15	19	10	19	9	19						
	6-20	10 15 20			6	15	14	22	4	12	15	19	15	6	15						
	6-25	15 20 25			9	16	18	27	6	15	19	10	19	9	19						
	6-32	20 25			9	16	18	27	6	15	19	10	19	9	19						
NBMR	8-32	15 25			9	16	18	27	6	15	19	10	19	9	19						
	8-32	15 25			9	16	18	27	6	15	19	10	19	9	19						



Threaded, Tapped

Part Number		L Selection		Knob Color	H	S	d	d1	Mass (g)		Unit Price	
Type	M (Coarse)	NKRM	NKRF						NKRM	NKRF	NKRM	NKRF
Threaded NKRM	5	10 16 20	10	32	22	10	15	9	13-15	15		
	6	10 16 20 25	15	40	25	11	17	10	20-22	17		
	8	16 20 25	18	50	30	13.5	20	12	36-40	27		
	10	30 50	20	63	35	15	23	16	78-90	55		
Tapped NKRF	5	10 16 20	10	32	22	10	15	9	13-15	15		
	6	10 16 20 25	15	40	25	11	17	10	20-22	17		
	8	16 20 25	18	50	30	13.5	20	12	36-40	27		
	10	30 50	20	63	35	15	23	16	78-90	55		

Part Number		L Selection		Knob Color	H	S	d	d1	C	f	Mass (g)	Unit Price
Type	RH8	NKRM	NKRF									
H8 Hole NKRR	8	40	15	25	9	11	19	14	2.8	7	31	
	10	50	19	32	13	15.5	22	17	2.8	8	48	
	12	63	23	40	17	20	26	21	3.8	10	89	

Ordering Example	Part Number	-	L	-	Knob Color
	NBMX3-16	-	10	-	B
	NKRM8	-	16	-	B
	NKRR12	-	16	-	B