

Panel Brackets - Plastic / Panel Clamping Brackets

Panel Brackets


Aluminum Type

Panel Brackets - Plastic



Material: Polyamide RoHS10


HCBR5 (Light Gray) **HCBR6** (Light Gray) **HCBR8** (Light Gray) **HCBR8-45** (Light Gray)
HCBRB5 (Black) **HCBRB6** (Light Gray) **HCBRB8** (Black) **HCBRB8-45** (Black)
HCBRB6 (Black) **HCBRB6S** (Black)




M5 insert nut is included inside. Use M5 screw with length 15 to attach panels.



Example
 Since Plastic Type HCBR5 has an eccentric T-shaped stopping part, it can be used for both panels with thickness 5mm and 3mm.



Plastic Type Mounting Method
 Easy installation by inserting the T-shaped stopping part into the slot and turning 90°. Use mounting screws with L dimension 15 for plastic types.



Part Number	Type	No.	Mass	A	Difference between the Extrusion Side and Attachment Face	Unit Price	Volume Discount Rate
HCBR HCBRB		5	4.3	12	3 or 5		
		6	6.8	20	5		
		6S	6.0	24	3		
		8	10.9	30	5		
		8-45*	13.2	35	5		


* Select No. 8 for 45 Square Light type (HFSL8-45) series.

Ordering Example **Part Number**
HCBR6

Panel Clamping Brackets



Material: Polyamide RoHS10




HCBS8 is commonly used for 8 Series and 8-45 Series. Panel thickness is adjustable by moving P part.

Part Number	Type	No.	Mass	P	Applicable Panel Thickness	Unit Price	Volume Discount Rate
HCBS		5	2.6		3~5		
		6	3.9				
		8	6.3				

How to Mount Panel Clamps

- Connection with Extrusion
 Easy installation by inserting the T-shaped stopping part into the slot and turning 90°.
- Connection with Panel
 As shown on the right, insert a panel into P part and push the moving part against the panel. Hole machining on the panel is not necessary.



Ordering Example **Part Number**
HCBS8

Panel Brackets - Aluminum




Material: A6063S-T5
 Surface Treatment: Anodize

HCBA5
HCBAB5 (Black Anodize)

HCBA6
HCBA6S
HCBA8
HCBAB6 (Black Anodize)
HCBAB6S (Black Anodize)
HCBA8 (Black Anodize)

HCBAN6 (1-Point Stopper Type)
HCBAN8 (1-Point Stopper Type)



Part Number	Type	No.	Mass	Difference between the Extrusion Side and Attachment Face	S	T	Y	Screw, Nut		Unit Price	Volume Discount Rate	
								Screw	Nut			
HCBA		5	19	3	-			CBM5-20	HNTT5-5			
		6		5	10			CBM6-12	2 HNTT6-6	2		
		6S	17	3	12			CBM6-15	HNTT8-6			
HCBA		8*		5*2	15			CBM6-15	HNTT8-6			
	HCBA		5	19	3	-			CB5-20	HNTT5-5		
			6		5	10			CB6-12	2 HNTT6-6	2	
		6S	17	3	12			CB6-15	HNTT8-6			
HCBA		8*		5*2	15			CB6-15	HNTT8-6			
	HCBA		6	18	5	10	3	7.8	HFBCM6-12	1 HNTT6-6	1	
			8		5*2	15	4	9.8	HFBCM6-15	1 HNTT8-6	1	
		8		5*2	15	4	9.8	HFBCM6-15	1 HNTT8-6	1		


8 is used in common with 8-45. *5*2 is for 40 square aluminum extrusions.
 Use Panel Mounting Screws (P787) for panel mounting.

Ordering Example **Part Number**
HCBA6
 Alterations **Part Number** - (SET)
HCBA6 - SET


Alteration	Code	Spec.	Bracket	Screw, Nut			
				For Extrusion Fitting		For Panel Fitting	
				Screw	Nut	Screw	Nut
Applicable Screw and Nut Set	SET	Applicable screws and nuts come in a set. When SET is specified, the product is not RoHS compliant.	HCBA5	CBM5-20	HNTT5-5		
			HCBA6	CBM6-12	HNTT6-6		HCBM5-10 (P787)
			HCBA6S	CBM6-12	HNTT6-6		
			HCBA8	CBM6-15	HNTT8-6	2	
			HCBA5	CB5-20	HNTT5-5		HCBM5-10 (P787)
			HCBA6	CB6-12	HNTT6-6		
			HCBA6S	CB6-12	HNTT6-6		
			HCBA8	CB6-15	HNTT8-6		
HCBAN6	HFBCM6-12	HNTT6-6	1		HCBM5-10 (P787)		
HCBAN8	HFBCM6-15	HNTT8-6	1				



Example of HCBA




Example of HCBAN




Panel Brackets Length Configurable Aluminum Long



Material: A6063S-T5
 Surface Treatment: Anodize RoHS10



When Alteration CTW45 is specified, the M5 Mounting Hole will be provided at 20mm from the end.



The clearance between the extrusion and panel can be filled. Use for reinforcements also.

Part Number	Type	No.	L 1mm Increment	Difference between the Extrusion Side and Attachment Face	S	Screw, Nut		Unit Price				
						Screw	Nut	L50-300	L301-700	L701-1100	L1101-1500	L1501-2000
HCBAL		6		5	10	CBM6-12	2 HNTT6-6					
		6S	50-2000	3	12	CBM6-15	2 HNTT8-6					
		8*		5*2	15	CBM6-15	2 HNTT8-6					

8 is used in common with 8-45. *5*2 is for 40 square aluminum extrusions.
 Use Panel Mounting Screws (P787) for panel mounting.

Ordering Example **Part Number** - L
HCBAL6 - 1000

Alterations **Part Number** - L - (CTW45, MH)
HCBAL6 - 500 - CTW45
HCBAL8 - 700 - MH

Alteration	Code	Spec.
Panel Brackets - Aluminum Long Cut 45 Degrees on Upper Slot	CTW45	Cuts in 45 degrees on both ends of Panel Brackets - Aluminum Long Type. Mounting Example
One Mounting Hole Addition	MH	Adds one M5 mounting hole on the middle of L Dimensions.

Caution: Cut edges are sharp.