


Pull Handles for Aluminum Extrusions

Pull Handles for Aluminum Extrusions / Pull Handles for Panels


Arched Pull Handles



UWSD



Features: Products intended for aesthetics as well as easier grip design.



MMaterial: SUS304 Equivalent
SSurface Treatment: Buffed Finish


Part Number		L ₁	H	h	H ₁	Allowable Load (N)	Mass (g)	Unit Price
Type	L							
UWSD	100	139	42	27	22	500	337	
	150	190	44	29	20		434	



Cast Pull Handles



UWASND



MMaterial: SUS304 Equivalent
SSurface Treatment: Buffed Finish

Back Side


Part Number		L ₁	H	h	T	A	W	R	N		Allowable Load (N)	Mass (g)
Type	L								Through	Countersink		
UWASND	80	96						20			500	97
	100	116	32	20	6	18	12	23	4.5	8.5		116
	150	170	46	30	9	22	16	30	6.5	12.5		301
	200	220	46	30	9	22	16	30	6.5	12.5		354

Ordering Example
Part Number
UWSD100
UWASND80

Aluminum Pull Handles



Type	M	S
HHDF	Aluminum Alloy	Electrostatic Paint (Mat Black)
HHDFL	Aluminum Alloy	Barrel Grinding
HHDFA	Aluminum Alloy	Buffed Finish



Part Number		Applicable Extrusion (Series)	L	L ₁	H	h	R	C	L _r	Mass (g)	Screw, Nut				Unit Price		
Type	A										Screw	Quantity	Nut	Quantity	HHDF	HHDFL	HHDFA
HHDF HHDFL HHDFA	19	HFS5	90	107	41	29	5.3	9	5	64	CBM5-10	2	HNTT5-5	2			
	20	HFS6	93.5	112	44	31	6.5	10.5	5	110	CBM6-12		HNTT6-6				
	26	HFS8 HFS8-45	130	149	57	40	8.5	13.3	5	250	CBM8-15		HNTT8-8				

Ordering Example
Part Number
HHDF19

Alterations
Part Number
HHDF19
(SET, SST)
SET


Alteration	Code	Spec.	No.
Applicable Screw and Nut Set	SET	Applicable screws and nuts come in a set.	19
	SST	When SST is specified, screws and nuts will be in stainless steel.	20
	(Stainless Steel)		26

Nylon Pull Handles



UPCN

(Nylon 6)



MMaterial
Glass Fiber Reinforced Nylon 6

Part Number		Color of Handle	H	Applicable Extrusion (Series)	h	L	L ₁	R	C	L _r	L _c	Allowable Load (N)	Mass (g)	Unit Price							
Type	A													1-9 pc(s)	10-14	15-19	20-50	W (White)	M (Orange)	R (Red)	G (Green)
UPCN	19		36	HFS5	30	90	108.5	5.5	9.5	11	6	500	23								
	21		51	HFS6	45	93.5	112	6.5	10.5	13	7		24								
	26	B (Black)	36		45								25								
	27	W (White)	41		50	117	139		8.5	13.3	15		28								
	28	M (Orange)	57		37						9		28								
		R (Red)	45		50								38								
		G (Green)	63	HFS8-45	55	132	156				16		48								
			52		42	152	177	6.5	10.5	13	7		54								
			70		42	179	204	8.5	13.3	17	9		62								
			51		63								66								
			71										68								
													86								

The default color of handle will be black unless specified. The default H dimension will be A19-H36, A21-H36, A26-H41, A27-H45 and A28-H50 unless specified.

Ordering Example
Part Number
UPCN19
Color of Handle
B
H
51

Alterations
Part Number
UPCN21
Color of Handle
B
H
51
(SET, SST)
SET


Alteration	Code	Spec.	No.
Applicable Screw and Nut Set	SET	Applicable screws and nuts come in a set.	19
	SST	When SST is specified, screws and nuts will be in stainless steel.	21
	(Stainless Steel)		26

When SET is specified, the product is not RoHS compliant.

Mounting Plates for Nylon Pull Handles



UPCNAT




MMaterial: SUS304

Part Number	L	L ₁	A	B	N	Handle	Reference Mass (g)	Unit Price 1 ~ 9 pc(s)	Volume Discount Rate 10-200
UPCNAT	90	108.5	19	9.25	5.5	UPCN19	31		
	93.5	112	21		6.5	UPCN21	36		
	117	139	26	11		UPCN26	55		
	132	156	27	12	8.5	UPCN27	64		
	179	204	28	12.5		UPCN28	88		

Ordering Example
Part Number
UPCNAT117


Example
UPCNAT93.5



Pull Handles for Panels



HHDS HHDSW HHDSA HHDSS



Type	M	S
HHDS	Polycarbonate (Black)	-
HHDSW	Polycarbonate (White)	-
HHDSA	ADC12	Baked Finish, Silver Metallic
HHDSS	SUS304 Equivalent	Buffed Finish

Part Number		L	L ₁	H	h	A	Mass (g)			Unit Price			
Type							HHDS, HHDSW	HHDSA	HHDSS	HHDS	HHDSW	HHDSA	HHDSS
HHDS HHDSW HHDSA HHDSS	90	110	32	24	13		17	43	90				
	104	127	37	27.7	16		25	65	150				
	122	149	43.3	32.5	19		42	102	220				

Ordering Example
Part Number
HHDS90

