

Timing Pulleys - XL

For Timing Belts, see **P. 1497**. For Keyless Timing Pulleys, see **P. 1479**.

Type	Belt Width				Material*1		Surface Treatment	Accessory*1 Set Screws
	6.4mm (1/4inch)	7.9mm (5/16inch)	9.5mm (3/8inch)	12.7mm (1/2inch)	Pulley	Flange		
ATP	XL025	XL031	XL037	XL050	Aluminum Alloy	Aluminum Alloy	Clear Anodize	SUS304
BTP							Black Anodize	
KTP							Hard Clear Anodize*2	
NTP							Electroless Nickel Plating	
MTP		-			S45C Equivalent	SPCC	-	SCM435 (Black Oxide)
MTPB		-					Black Oxide	
MTPP		-					Electroless Nickel Plating	
STP		-					-	
					SUS304	SUS304	-	SUS304

*1 Materials for pulleys and accessories may be changed to the equivalent ones. *2 Hard Clear Anodize: Film Hardness 300HV ~.
 * Flange is already swaged, and set screws are included with for Shaft Bore P, N and C.

Tooth Profile (ISO Standard Rack Dimensions)

