

Welded Thin-Walled Hollow Tubes / Drawn Hollow Tubes

Material: SUS304 / STKM13A, C2700, A6063

Thin-Walled Ground Stainless Steel Hollow Tubes / Thin-Walled Ground Stainless Steel Hollow Tubes

Precision I.D. / O.D.

Welded Thin-Walled Hollow Tubes



Drawn Hollow Tubes




Type	Hollow Tube Type	Material
PIPD	Welded Tube	SUS304
PIPC	Drawn Hollow Tube	STKM13A
PIPG		C2700 (Brass)
PIPA		A6063


D	PIPC	PIPG	PIPA
2-6	±0.1	±0.1	
8-30	±0.2	±0.4	

L	PIPC	PIPG	PIPA
10	±0.2		
31	±0.3		
121	±0.5		
401	±0.8		

PIPD



PIPC, PIPG, PIPA




For maximum L dimension in each D dimension, refer to the specification table.

Part Number		L 1mm increment	t	Unit Price					
Type	D			L10~100	L101~200	L201~400	L401~600	L601~800	L801~1000
PIPD (SUS304)	2	10~1000	0.5						
	3								
	4								
	5								
	6								
	8								
	10								
	12								
	15								
	16								
	20								
	25								
	30								
PIPC (STKM13A)	5	10~250	1				-	-	-
	6	10~500							
	8								
	10								
	12	10~900	1						
	13		1.5						
	15		1.5						
	16		1						
	20	10~1000	1						
	25		2						
30	2								
PIPG (C2700)	5	10~250	1				-	-	-
	6	10~500							
	8								
	10								
	12	10~900	1						
	13		1.5						
	15		1.5						
	20		1						
	25	10~1000	2						
	30		2						
PIPA (A6063)	5	10~250	1				-	-	-
	6	10~500							
	8								
	10								
	12	10~900	1						
	13		1.5						
	15		1.5						
	16		2						
	20	10~1000	1						
	25		2						
30	2								


Ordering Example
Part Number - L
PIPC8 - 450

Example



Type	Material
SPLS	SUS304
SPLT	SUS304 (Annealed)

SPLS: t=0.3, 0.5, 1.0 Selection
SPLT: t=0.5 only



L Dimension Tolerance		
or More	or Less	Tolerance
10	30	±0.2
31	120	±0.3
121	400	±0.5
401	1000	±0.8

D Dimension Tolerance		
or More	or Less	Tolerance
2	12	0 -0.05
15	30	0 -0.1


Part Number	Type	D			L 1mm increment	Unit Price					
		t=0.5	t=0.3	t=1.0		L10~50	L51~100	L101~200	L201~400	L401~600	L601~800
SPLS SPLT		2	2A	-	10~1000						
		3	3A	-							
		4	4A	4B							
		5	5A	5B							
		6	6A	6B							
		8	8A	8B							
		10		10B							
		12									
		15									
		16									
		20									
		25									
		30									

For SPLT, t=0.5 only.

Ordering Example

Part Number - L
SPLS2A - 500
SPLT4 - 500

Example




[Product Applications]
Roll Shafts for Photocopiers
Antenna
For heating
For plumbing
Injection Nozzle
Ornamental Piping, etc.

SPLS is a Straight Type and can be used for injecting or other purposes. Annealed material (180 to 220HV) is adopted so that SPLT can be bent to fit the above applications.

Precision I.D./O.D.



SPLN



D and d Dimension Tolerance	
D	(d)
0.5~2.0	±0.01
2.5~5.0	±0.02

Material: SUS304

Part Number	Type	D	L 1mm increment	(d)	Unit Price		
					L10~50	L51~100	L101~200
SPLN		0.5	10~200	0.34			
		1		0.7			
		1.5		1.1			
		2		1.6			
		2.5		2.1			
		3		2.6			
		3.5		3.1			
		4		3.6			
		4.5		4.1			
		5		4.6			

Ordering Example

Part Number - L
SPLN2 - 100