

SLIDE TYPE AIR NIPPERS

-HORIZONTAL SLIDE TYPE-

Blade sold separately


shows in red

■ Horizontal Slide Type



⚠ The blade is sold separately. Note that there are a regular blade and a reverse blade.

MGT-NY□□ (Pull type)
MGT-NY□□R (Push type)



Cutting capacity φ (mm)		Air consumption (cm ³ /time)	Weight (g)	Slide type	Part dimensions (mm)										Tube Outer × Inner	Hose Port	Part Number	Unit Price 1~9 pcs	
Soft resin	Hard resin				A	B	C	D	E	F	G	H	I	J					
3.0	2.0	48.0	155.0	Pull 0~3	8.6	75.9	40.9	25.0	10.0	15.0	M4	23.0	47.6	3.0	4 × 2.5	Hose nipple	MGT-NY05	Quotation	
				Push 0~3												Tube fitting	MGT-NY05R-4		
3.5	2.3	68.0	210.0	Pull 0~3	8.8	82.1	42.1	30.0	10.0	20.0	M4	28.0	51.6	5.0		Hose nipple	MGT-NY10		
				Push 0~3												Tube fitting	MGT-NY10R-4		
4.0	2.6	136.0	319.0	Pull 0~3	10.2	93.0	48.0	35.0	10.0	25.0	M4	33.0	58.0	5.0		Hose nipple	MGT-NY15		
				Push 0~3												Tube fitting	MGT-NY15R-4		
5.0	3.4	184.0	580.0	Pull 0~5	12.5	108.5	54.5	40.0	14.0	30.0	M5	42.0	69.0	2.0		6 × 4	Hose nipple		MGT-NY25
				Push 0~5													Tube fitting		MGT-NY25R-6

• Operating air pressure: 0.4~0.5 MPa

⚠ For quantities not displayed here, refer to our MISUMI website for more information.



Order

Part Number

MGT-NY05
MGT-NY03G

Days
to Ship

Quotation



Price

Quotation