

ROUND AIR NIPPERS

Blade sold separately


shows in red

*Some products may not be available, please contact your local MISUMI Sales Office for more information.

■ Round Type



MGT—NR□□



ⓘ The blade is sold separately. *For details, see P.191

Cutting capacity ϕ (mm)				Air consumption (cm ³ /time)	Weight (g)	Part dimensions (mm)				Part Number	Unit Price 1~9 pcs
Soft resin	Hard resin	Copper wire	Iron wire			A	B	G	F		
2.0	-	1.0	0.5	45	70	110	23	17	M3×8	MGT—NR3	Quotation
2.0	-	1.0	0.5	64	110	94	30	20	M4×10	MGT—NR5	
3.0	2.0	1.6	1.0	116	150	113	34	22	M4×10	MGT—NR7	
4.0	2.6	1.8	1.2	116	215	113	36	24	M4×10	MGT—NR10L	
7.0	5.0	2.6	2.0	230	280	129	45	30	M5×12	MGT—NR20	
10.0	6.5	3.3	2.8	584	505	165	56	40	M6×12	MGT—NR30	
12.0	6.5	5.5	4.5	1170	1190	222	75	50	M8×12	MGT—NR50	

- Operating air pressure MGT—NR10L: 0.5~0.6 MPa
- Applicable air hose inner diameter: 5 mm

ⓘ For quantities not displayed here, refer to our MISUMI website for more information.



Order

Part Number

MGT—NR3

Days
to Ship

Quotation



Price

Quotation

SQUARE AIR NIPPERS

Blade sold separately


shows in red

*Some products may not be available, please contact your local MISUMI Sales Office for more information.

■ Square Type



MGT-NS□□



* The blade is sold separately. * For details, see P.191

Cutting capacity ϕ (mm)				Air consumption (cm ³ /time)	Weight (g)	Part dimensions (mm)								Part Number	Unit Price 1~9 pcs
Soft resin	Hard resin	Copper wire	Iron wire			A	B	C	D	E	F	G	H		
2.0	-	1.0	0.5	45	95	110	23	40	19	40	M3×8	17	M3×3.5	MGT-NS3	Quotation
2.0	-	1.0	0.5	64	135	94	30	30	24	34	M4×10	20	M3×5	MGT-NS5	
3.0	2.0	1.6	1.0	116	215	113	36	30	28	18	M4×10	24	M4×5.5	MGT-NS7	
4.0	2.6	1.8	1.2	116	215	113	36	30	28	38	M4×10	24	M4×5.5	MGT-NS10L	
7.0	5.0	2.6	2.0	230	370	129	45	40	36	19	M5×12	30	M4×7	MGT-NS20	
10.0	6.5	3.3	2.8	584	685	170	56	60	46	20	M6×12	40	M5×10	MGT-NS30	
7.0	5.0	2.6	2.0	230	455	129	45	40	36	230	M5×12	30	M4×7	MGT-NS20H-1	

- Operating air pressure MGT-NS3/5: 0.4~0.5 MPa, MGT-NS10L: 0.5~0.6 MPa
- Air inlet screw thread diameter Rc(PT) 1/8 · Applicable air hose inner diameter: 5 mm

* For quantities not displayed here, refer to our MISUMI website for more information.



Order

Part Number
MGT-NS3Days
to Ship

Quotation



Price

Quotation