


SUCTION CUP (SPONGE TYPE)

■ Suction Cup (Sponge type)




VC—NS


No.8




No.12




No.15




No.20



No.30



No.40



M Body: Silicone
 Sponge: Single layered silicone
H Shore A50~70
 Specification Temperature -70°C~200°C
 Maximum Operating Temperature 120°C

Applicable metal fittings	Mounting type	Cup dia.	Weight (g) ^{*1}	Part Number		Unit Price 1~30 pcs
				Type	No.	
VC—KNG7 VC—KNGB7 VC—KNG11 VC—KNGB11	Embedded type	8	1	VC—NS (Flat)	8	Quotation
		12	1		12	
		15	3		15	
		20	4		20	
		30	4		30	
		41.5	8		40	

*1 The weight is an approximate value which serves only as a guideline.



Order

Part Number
VC—NS12



Days to Ship

Quotation



Price

Quotation

